

FlowConnector[™] Kits - Investigator

FlowConnector[™] Kits - Investigator[™] connect your WaterSep Investigator[™] cartridge to your tubing and pump. The kits come with or without PendoTECH pressure sensors that enable monitoring of transmembrane pressure (TMP).




Diagram: FlowConnector[™] Kit- Investigator[™] without sensors

ORDERING INFORMATION

Place orders or request quotes online at www.watersep.net or email purchase orders to orders@watersep.net.

FlowConnector[™] Kits - Investigator[™] without sensors

FlowConnector[™] Kit - Investigator[™] Green

FlowConnector[™] Kit - Investigator[™] Steamer

FlowConnector[™] Kit - Investigator[™] ReUse

Product Code: FC INV KIT-000 01

Includes:

For Retentate/Feed

Item 2: (2) 1½" TC Clamps

Item 4: (2) 1½" TC x ½" Barb (Reducer)

Item 6: (4) 1½" TC Silicone Gaskets (2 extra not shown)

For Retentate

Item 8: (1) ¾" Pinch Valve

For Permeate

Item 1: (2) ¾" TC White Plastic Clamps

Item 3: (1) ¾" TC x ⅜" Barb (Reducer)

Item 5: (4) ¾" TC Silicone Gaskets (2 extra not shown)

Item 7: (1) ⅜" Pinch Valve

Item 9: (1) ¾" TC Cap

FlowConnector™ Kits - Investigator™




Diagram: FlowConnector™ Kit- Investigator™ with sensors

FlowConnector Kits - Investigator™ with sensors

FlowConnector™ Kit - Investigator™ Green

FlowConnector™ Kit - Investigator™ Steamer

FlowConnector™ Kit - Investigator™ ReUse

Product Code: FC INV KIT-SEN 01

Includes:

For Retentate/Feed

Item 2: (2) 1½" TC Clamps

Item 4: (4) 1½" TC Silicone Gaskets (2 extra not shown)

Item 8: (2) 1½" TC x ½" Barb (Reducer)

Item 10: (2) Single Use Pressure Sensors ½" Barb

For Retentate

Item 6: (1) ¾" Pinch Valve

For Permeate

Item 1: (2) ¾" TC Clamps

Item 3: (4) ¾" TC Silicone Gaskets (2 extra not shown)

Item 5: (1) ⅜" Pinch Valve

Item 7: (2) ¾" TC Cap

Item 9: (1) Single Use Pressure Sensor ¾" TC to ⅜" Barb (Reducer)

MATERIALS OF CONSTRUCTION FOR KIT COMPONENTS

IN FLUID CONTACT

Gaskets:

Platinum-cured silicone

Reducers and Caps:

Polypropylene AF

Sensors:

Polysulfone

NOT IN FLUID CONTACT

Pinch Valves:

Glass Reinforced White Nylon

Clamps:

Glass Reinforced White Nylon

Technical Support: experttalk@watersep.net
or call 508.970.0089 x 204